



JKD1125MID

125A Pulsed & ModBus Meter MID Extension Box

Technical characteristics

Architecture

Type of pole	3P+N
--------------	------

Electric current

Rated current	125 A
---------------	-------

Capacity

Number of modules	4
-------------------	---

Dimensions

Height	300 mm
Width	465 mm
Depth	132.50 mm

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Measurement

Measuring system	Measurement transformer
Type of measuring instrument	Digital
Current measurement range	5 - 6,000 A

Power supply

Number of phases for power supply	3
-----------------------------------	---

Functions

Accuracy class	0.005
Tariff type	Multi-tariff
Is calibrated	Yes

Safety

Ingress Protection (IP) class	IP2XC
-------------------------------	-------

Use conditions

Operating temperature	-10 - 55 °C
Storage/transport temperature	-20 - 75 °C

Frequency

Frequency	50 - 50 Hz
-----------	------------