



JKD1125MID

125A Pulsed & ModBus Meter MID Extension Box

Technical characteristics

Architecture

Number of poles	2 P
Fixing mode	surface-mounting

Main electrical features

Frequency	50 Hz
Type of supply voltage	AC

Dimensions

Depth of installed product	132.5 mm
Height of installed product	300 mm
Width of installed product	465 mm

Measurement

Type of measuring instrument	digital
------------------------------	---------

Materials

Colour	light grey
--------	------------

Equipment

Type of display	LCD
-----------------	-----

Safety

Protection class	isol.class I
------------------	--------------

Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------