



JKD1164PM

125A Dual Metered TPN Power/Lighting Board. Lower Pan 16 Way/Upper Pan 4 Way

Technical Characteristics

Fixing mode	surface-mounting
Rated current	125 A
Depth of installed product	165 mm
Height of installed product	1400 mm
Width of installed product	465 mm
Number of modules	60
Type of door closing	Quarter turn lock
Interlockable	No
Colour	RAL 7035
Material	Steel
Can be accessorized	No
European directive WEEE	concerned
Protection index IP	IP30
Protection class	Protection class III