



JKD125TMID

125A Triple Multi Function MID Metered Incomer. Pulsed and Modbus. Side by Side

Technical characteristics

Architecture

Fixing mode	surface-mounting
-------------	------------------

Main electrical features

Frequency	50 Hz
-----------	-------

Dimensions

Depth of installed product	132.5 mm
Height of installed product	625 mm
Width of installed product	1395 mm

Cover, door

Type of door closing	Quarter turn lock
Interlockable	No

Materials

Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	Steel

Equipment

Can be accessorized	Yes
---------------------	-----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP30
Protection class	isol.class I

Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------