



JKD168MID

125A Dual Metered MID TPN Power/Lighting Board. Lower Pan 6 Way/Upper Pan 8 Way

Technical Characteristics

Fixing mode	surface-mounting
Frequency	50 Hz
Rated current	125 A
Depth of installed product	165.5 mm
Height of installed product	1250 mm
Width of installed product	465 mm
Number of modules	42
Type of door closing	Quarter turn lock
Interlockable	No
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	Steel
Can be accessorized	Yes
European directive WEEE	concerned
Protection index IP	IP30
Operating temperature	-10...55 °C