



JKD188TM

125A Power/Lighting Board 8/8 Way Pan Assemblies Modbus Comms

Technical characteristics

Architecture

Fixing mode surface-mounting

Main electrical features

Frequency 50 Hz

Dimensions

Depth of installed product 165.5 mm

Height of installed product 1250 mm

Width of installed product 465 mm

Cover, door

Type of door closing Quarter turn lock

Interlockable No

Materials

Colour light grey

RAL colour RAL 7035 - Light grey

Material Steel

Equipment

Can be accessorized Yes

Standards

European directive WEEE concerned

Safety

Protection index IP IP30

Use conditions

Operating temperature -10...55 °C