



JKD2250MID

## 250A Pulsed ModBus Meter MID Extension Box

### Technical characteristics

#### Architecture

Fixing mode	surface-mounting
-------------	------------------

#### Main electrical features

Frequency	50 Hz
-----------	-------

#### Dimensions

Depth of installed product	300 mm
Height of installed product	165.5 mm
Width of installed product	465 mm

#### Measurement

Type of measuring instrument	digital
------------------------------	---------

#### Materials

Colour	light grey
--------	------------

#### Equipment

Type of display	LCD
-----------------	-----

#### Safety

Protection class	isol.class I
------------------	--------------

#### Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------