



JKM02

Multifunction measurement device DIN rail 2x3-Phase RS485

Technical characteristics

Architecture

Bus system	MODBUS
Type of pole	4P

Capacity

Number of modules	4
-------------------	---

Dimensions

Height	90 mm
Width	70 mm
Depth	62 mm

Main electrical attributes

Type of pulse generator	Electrical
-------------------------	------------

Compatibility

Suitable for	Purchase
--------------	----------

Connection

Connector/plug type Bus system	Pulse, RS485
--------------------------------	--------------

Measurement

Measuring system	Measurement transformer
Type of measuring instrument	Electronic
Measurement range voltage Ph-N	60 - 300 V
Measurement range voltage Ph-Ph	104 - 520 V
Frequency measuring range	45 - 65 Hz

Functions

Accuracy class	B
Tariff type	One-tariff

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	-10 - 55 °C
Storage/transport temperature	-20 - 75 °C