



JN201MID

JN Multifunction Meter Pack 250A Pulsed and Modbus MID

Technical characteristics

Architecture

Type of pole 3P+N

Main electrical features

Frequency 50 Hz

Type of supply voltage AC

Dimensions

Depth of installed product 66 mm

Height of installed product 118.5 mm

Width of installed product 70 mm

Measurement

Type of measuring instrument digital

Power supply

Supply voltage 230/400 V +/- 15%

Equipment

Type of display LCD

Safety

Protection class Protection class III

Use conditions

Operating temperature -10...55 °C