



JN201MID

## JN Multifunction Meter Pack 250A Pulsed and Modbus MID

### Technical characteristics

#### Architecture

Type of pole 3P+N

#### Main electrical features

Frequency 50 Hz

Type of supply voltage AC

#### Dimensions

Depth of installed product 66 mm

Height of installed product 118.5 mm

Width of installed product 70 mm

#### Measurement

Type of measuring instrument digital

#### Power supply

Supply voltage 230/400 V +/- 15%

#### Equipment

Type of display LCD

#### Safety

Protection class Protection class III

#### Use conditions

Operating temperature -10...55 °C