



JN204BG

250A 4 Way 125A Outgoers Glazed

Technical characteristics

Architecture

Fixing mode surface-mounting

Dimensions

Depth of installed product 178.4 mm

Height of installed product 950 mm

Width of installed product 710 mm

Cover, door

Type of door closing Quarter turn lock

Door locking with key

Materials

Colour beige

RAL colour RAL 7035 - Light grey

Material Steel

Standards

European directive WEEE concerned

Safety

Protection index IP IP30

Protection class Protection class III