



JN212B

250A 12 Way 125A Outgoers Plain

Technical characteristics

Connection

Number of accessible phases 3

Installation, mounting

Suitable for outdoor usage No

Mounting on Surface mounting

Electric current

Rated current 250 A

Equipment

With lock No

Capacity

Number of modules 36

Functions

Has protection main switch No

Dimensions

Height 1,250 mm

Width 710 mm

Depth 178.40 mm

Cover, door

Number of cabinet doors 1

Door/cover is transparent No

Materials

Material Steel

RAL code 7035, 9001

Colour Light grey

Safety

Protection class Isolation class III

Impact resistance IK IK05

Ingress Protection (IP) class IP30

Locking type Key lock, Quarter turn lock