



JN212BG

## 250A 12 Way 125A Outgoers Glazed

### Technical characteristics

#### Architecture

Fixing mode surface-mounting

#### Dimensions

Depth of installed product 178.4 mm

Height of installed product 1250 mm

Width of installed product 710 mm

#### Cover, door

Type of door closing Quarter turn lock

Door locking with key

#### Materials

Colour beige

RAL colour RAL 7035 - Light grey

Material Steel

#### Standards

European directive WEEE concerned

#### Safety

Protection index IP IP30

Protection class Protection class III