



JN216B

250A 16 Way 125A Outgoers Plain

Technical characteristics

Installation, mounting

| | |
|----------------------------|------------------|
| Suitable for outdoor usage | No |
| Mounting on | Surface mounting |

Electric current

| | |
|---------------|-------|
| Rated current | 250 A |
|---------------|-------|

Equipment

| | |
|-----------------------------|-----|
| With lock | No |
| Has neutral terminal block | Yes |
| Has earthing terminal block | Yes |

Dimensions

| | |
|--------|-----------|
| Height | 1,550 mm |
| Width | 710 mm |
| Depth | 178.40 mm |

Cover, door

| | |
|---------------------------|----|
| Number of cabinet doors | 1 |
| Door/cover is transparent | No |

Materials

| | |
|----------|------------|
| Material | Steel |
| RAL code | 7035, 9001 |
| Colour | Light grey |

Safety

| | |
|-------------------------------|-----------------------------|
| Protection class | Isolation class III |
| Impact resistance IK | IK05 |
| Ingress Protection (IP) class | IP30 |
| Locking type | Key lock, Quarter turn lock |