



Insulated busbar 2P 63A prong 10mm² 24M

Technical characteristics

Architecture

Number of poles 2 P

Main electrical features

Rated operational voltage U_e 230 / 400 V

Voltage

Max operating voltage 400 V

Rated impulse withstand voltage 4 kV

Connection

Connection cross-sect. rigid cable 10mm²

Standards

European directive WEEE concerned

KB263C