



KB363A

### Insulated busbar 3P 63A prong 10mm<sup>2</sup> 12M

#### Technical characteristics

##### Architecture

Number of poles	3 P
Type of pole	3 P

##### Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

##### Voltage

Max operating voltage	400 V
Rated impulse withstand voltage	4 kV

##### Connection

Connection cross-sect. rigid cable	10mm <sup>2</sup>
Type of connection	with screw