



KB363C

Insulated busbar 3P 63A prong 10mm² 24M

Technical characteristics

Architecture

Number of poles	3 P
Type of pole	3 P

Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

Voltage

Max operating voltage	400 V
Rated impulse withstand voltage	4 kV

Connection

Connection cross-sect. rigid cable	10mm ²
Type of connection	with screw