



KB463A

**Insulated busbar 3P+N 63A prong 10mm<sup>2</sup> 12M**

**Technical characteristics**

**Architecture**

Number of poles	4 P
Type of pole	3P+N

**Main electrical features**

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

**Voltage**

Max operating voltage	400 V
Rated impulse withstand voltage	4 kV

**Materials**

Colour	stone grey
--------	------------

**Connection**

Connection cross-sect. rigid cable	10mm <sup>2</sup>
Type of connection	with screw

**Standards**

European directive WEEE	concerned
-------------------------	-----------