



KB463A

Insulated busbar 3P+N 63A prong 10mm² 12M

Technical characteristics

Architecture

Number of poles 4 P

Main electrical features

Rated operational voltage Ue 230 / 400 V

Voltage

Max operating voltage 400 V

Rated impulse withstand voltage 4 kV

Materials

Colour stone grey

Connection

Type of connection with screw

Standards

European directive WEEE concerned