



KB463A

**Insulated busbar 3P+N 63A prong 10mm<sup>2</sup> 12M**

**Technical characteristics**

**Architecture**

|                 |      |
|-----------------|------|
| Number of poles | 4 P  |
| Type of pole    | 3P+N |

**Main electrical features**

|                              |             |
|------------------------------|-------------|
| Rated operational voltage Ue | 230 / 400 V |
|------------------------------|-------------|

**Voltage**

|                                 |       |
|---------------------------------|-------|
| Max operating voltage           | 400 V |
| Rated impulse withstand voltage | 4 kV  |

**Connection**

|                                    |                   |
|------------------------------------|-------------------|
| Connection cross-sect. rigid cable | 10mm <sup>2</sup> |
| Type of connection                 | with screw        |