



KB480B

Insulated busbar 3P+N 80A prong 16mm² 57M

Technical characteristics

Architecture

Number of poles	4 P
Type of pole	3P+N

Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

Voltage

Max operating voltage	400 V
Rated impulse withstand voltage	4 kV

Connection

Connection cross-sect. rigid cable	16mm ²
Type of connection	with screw