



KB480B

Insulated busbar 3P+N 80A prong 16mm² 57M

Technical characteristics

Architecture

| | |
|-----------------|------|
| Number of poles | 4 P |
| Type of pole | 3P+N |

Main electrical features

| | |
|--|-------------|
| Rated operational voltage U _e | 230 / 400 V |
|--|-------------|

Voltage

| | |
|---------------------------------|-------|
| Max operating voltage | 400 V |
| Rated impulse withstand voltage | 4 kV |

Materials

| | |
|--------|------------|
| Colour | stone grey |
|--------|------------|

Connection

| | |
|------------------------------------|-------------------|
| Connection cross-sect. rigid cable | 16mm ² |
| Type of connection | with screw |

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|