



KDN263B

Insulated busbar 2P 63A fork 10mm² 57M

Technical Characteristics

Number of poles	2 P
Rated operational voltage Ue	230 / 400 V
Rated current	63 A
Max operating voltage	400 V
Length	1000 mm
Colour	stone grey
Connection cross-sect. rigid cable	10mm ²
Type of connection	with screw / quick connect
European directive WEEE	concerned
