



KDN463B

### Insulated busbar 4P 63A fork 10mm<sup>2</sup> 57M

#### Technical characteristics

##### Architecture

Number of poles 4 P

Type of pole 4 P

##### Main electrical features

Rated operational voltage U<sub>e</sub> 230 / 400 V

##### Voltage

Max operating voltage 400 V

##### Connection

Connection cross-sect. rigid cable 10mm<sup>2</sup>

Type of connection with screw / quick connect