



KF83B

**Connection terminal 1P prong 2x25mm<sup>2</sup>**

**Technical characteristics**

**Architecture**

Number of poles 1 P

**Voltage**

Max operating voltage 500 V

**Connection**

Connection cross-sect. flexible conductor 2x16mm<sup>2</sup>

Connection cross-sect. rigid cable 2x25mm<sup>2</sup>

Type of connection with screw