



KF83B

Connection terminal 1P prong 2x25mm²

Technical characteristics

Architecture

Number of poles	1 P
Fixing mode	Screwed

Voltage

Max operating voltage	500 V
-----------------------	-------

Materials

Material	Mixed materials
----------	-----------------

Connection

Connection cross-sect. flexible conductor	2x16mm ²
Connection cross-sect. rigid cable	2x25mm ²
Type of connection	with screw

Accessories included

Type of accessory	Connection clamp
-------------------	------------------

Standards

European directive WEEE	concerned
-------------------------	-----------