



KRN199

## Neutral connecting block 125A

### Technical characteristics

#### Architecture

Number of poles	1 P
Type of pole	N

#### Main electrical features

Rated operational voltage Ue	230 / 400 V
Type of supply voltage	AC

#### Voltage

Rated insulation voltage	440 V
Rated impulse withstand voltage	4 kV

#### Dimensions

Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

#### Installation, mounting

Tightening torque	3,6Nm
-------------------	-------

#### Use conditions

Operating temperature	-20...50 °C
-----------------------	-------------