



KRN199

Neutral connecting block 125A

Technical characteristics

Architecture

Number of poles	1 P
Type of pole	N

Main electrical features

Rated operational voltage Ue	230 / 400 V
Type of supply voltage	AC

Voltage

Rated insulation voltage	440 V
Rated impulse withstand voltage	4 kV

Dimensions

Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

Installation, mounting

Tightening torque	3,6Nm
-------------------	-------

Use conditions

Operating temperature	-20...50 °C
-----------------------	-------------