



LF316PV



PV Fuse-link 10x38 mm 1000V DC 16A

Technical Characteristics

Rated operational voltage Ue	0 / 1000 V
Rated current	16 A
Type of supply voltage	DC
Total power loss under IN	2.7 W
Can be accessorized	No
European directive WEEE	concerned
Operating temperature	-25...70 °C
