




MZ201



**Auxiliary contact 1C+1O 6A 240V AC**

**Technical characteristics**

**Main electrical features**

Rated operational voltage Ue	230 / 415 V
Type of supply voltage	AC

**Voltage**

Rated insulation voltage	4000 V
Max operating voltage	240 V

**Electric current**

Acceptable current rating with AC1	6 A
------------------------------------	-----

**Dimensions**

Depth of installed product	40 mm
Height of installed product	80 mm
Width of installed product	9.5 mm

**Power**

Total power loss under IN	0.1 W
---------------------------	-------

**Endurance**

Electric endurance in number of cycles	6000
Number of mechanical operations	12000

**Installation, mounting**

Tightening torque	1,2Nm
-------------------	-------

**Connection**

Connection cross-sect. flexible conductor	6mm <sup>2</sup>
Connection cross-sect. rigid cable	10mm <sup>2</sup>
Type of connection	with screw
Type of contacts	1NC+1NO

**Use conditions**

Operating temperature	-25...60 °C
-----------------------	-------------