



MZ201



Auxiliary contact 1C+1O 6A 240V AC

Technical characteristics

Main electrical features

Rated operational voltage Ue	230 / 415 V
Type of supply voltage	AC

Voltage

Rated insulation voltage	4000 V
Max operating voltage	240 V

Electric current

Acceptable current rating with AC1	6 A
------------------------------------	-----

Dimensions

Depth of installed product	40 mm
Height of installed product	80 mm
Width of installed product	9.5 mm

Power

Total power loss under IN	0.1 W
---------------------------	-------

Endurance

Electric endurance in number of cycles	6000
Number of mechanical operations	12000

Installation, mounting

Tightening torque	1,2Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	6mm ²
Connection cross-sect. rigid cable	10mm ²
Type of connection	with screw
Type of contacts	1NC+1NO

Use conditions

Operating temperature	-25...60 °C
-----------------------	-------------