




MZ202



## Alarm contact 1C+1O 6A 240V AC

### Technical characteristics

#### Electric current

|               |     |
|---------------|-----|
| Rated current | 6 A |
|---------------|-----|

#### Connectivity

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

#### Capacity

|                   |      |
|-------------------|------|
| Number of modules | 0.50 |
|-------------------|------|

#### Connection

|                                  |                    |
|----------------------------------|--------------------|
| Type of contacts                 | 1NC+1NO            |
| Cross-section flexible conductor | 6 mm <sup>2</sup>  |
| Cross-section rigid conductor    | 10 mm <sup>2</sup> |

#### Voltage

|                             |         |
|-----------------------------|---------|
| Rated insulation voltage Ui | 4,000 V |
| Type voltage supply         | AC      |

#### Endurance

|  |        |
|--|--------|
| Number of mechanical operations        | 12,000 |
| Electric endurance in number of cycles | 6,000  |

#### Use conditions

|                               |             |
|-------------------------------|-------------|
| Operating temperature         | -25 - 60 °C |
| Storage/transport temperature | -40 - 80 °C |

#### Power

|                           |        |
|---------------------------|--------|
| Total power loss under IN | 0.20 W |
|---------------------------|--------|

#### Dimensions

|       |       |
|-------|-------|
| Width | 9 mm  |
| Depth | 68 mm |

#### Equipment

|                        |   |
|------------------------|---|
| Number of INV contacts | 0 |
| Number of NC contacts  | 1 |