


MZ203



**Shunt trip 230-415V AC 110-130V DC**

**Technical characteristics**

**Main electrical features**

Rated operational voltage Ue	230 / 415 V
Frequency	50/60 Hz
Type of supply voltage	AC/DC

**Voltage**

Rated insulation voltage	4000 V
--------------------------	--------

**Dimensions**

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	18 mm

**Power**

Total power loss under IN	25.3 W
---------------------------	--------

**Installation, mounting**

Tightening torque	1,2Nm
-------------------	-------

**Connection**

Connection cross-sect. flexible conductor	6mm <sup>2</sup>
Connection cross-sect. rigid cable	10mm <sup>2</sup>

**Use conditions**

Operating temperature	-25...60 °C
-----------------------	-------------