


MZ203



Shunt trip 230-415V AC 110-130V DC

Technical characteristics

Main electrical features

Rated operational voltage Ue	230 / 415 V
Frequency	50/60 Hz
Type of supply voltage	AC/DC

Voltage

Rated insulation voltage	4000 V
--------------------------	--------

Dimensions

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	18 mm

Power

Total power loss under IN	25.3 W
---------------------------	--------

Installation, mounting

Tightening torque	1,2Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	6mm ²
Connection cross-sect. rigid cable	10mm ²

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-25...60 °C
-----------------------	-------------