




MZ204



## Shunt trip 24-48V AC 12-48V DC

### Technical characteristics

#### Power

|                       |       |
|-----------------------|-------|
| Inrush power absorbed | 27 VA |
|-----------------------|-------|

#### Use conditions

|                       |             |
|-----------------------|-------------|
| Operating temperature | -25 - 60 °C |
|-----------------------|-------------|

#### Voltage

|                             |           |
|-----------------------------|-----------|
| Command voltage AC          | 24 - 48 V |
| Command voltage DC          | 12 - 48 V |
| Type voltage supply         | AC/DC     |
| Rated insulation voltage Ui | 4,000 V   |

#### Dimensions

|        |       |
|--------|-------|
| Height | 83 mm |
| Width  | 18 mm |
| Depth  | 68 mm |