


MZ206



Under voltage release 230V AC

Technical characteristics

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz
Type of supply voltage	AC

Voltage

Rated insulation voltage	4000 V
--------------------------	--------

Electric current

Acceptable current rating with AC1	15 mA
------------------------------------	-------

Dimensions

Depth of installed product	68 mm
Width of installed product	17.5 mm

Power

Total power loss under IN	2 W
---------------------------	-----

Installation, mounting

Tightening torque	1,2Nm
-------------------	-------

Use conditions

Operating temperature	-25...60 °C
-----------------------	-------------