



MZ520N



Auxiliary contact for motor starter 1C+1O 230/400V AC

Technical characteristics

Main electrical features

Rated operational voltage U _e	220 / 500 V
Type of supply voltage	AC

Voltage

Rated insulation voltage	690 V
Rated impulse withstand voltage	6000 V

Electric current

Acceptable current rating with AC1	3 A
------------------------------------	-----

Dimensions

Depth of installed product	68 mm
Width of installed product	9 mm

Power

Total power loss under I _N	0.04 W
---------------------------------------	--------

Endurance

Electric endurance in number of cycles	50000
Number of mechanical operations	100000

Equipment

Number of auxiliary contacts as normally closed contact	1
Number of auxiliary contacts as normally open contact	1
Number of auxiliary contacts as change-over contact	0

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-25...55 °C
-----------------------	-------------