



MZ527N



Alarm contact for motor starter 2C

Technical characteristics

Main electrical features

Rated operational voltage Ue	220 / 500 V
Frequency	40/60 Hz
Type of supply voltage	AC

Voltage

Rated insulation voltage	690 V
Rated impulse withstand voltage	6000 V

Electric current

Acceptable current rating with AC1	3 A
------------------------------------	-----

Dimensions

Depth of installed product	68 mm
Width of installed product	9 mm

Power

Total power loss under IN	0.2 W
---------------------------	-------

Endurance

Electric endurance in number of cycles	5000
Number of mechanical operations	10000

Installation, mounting

Tightening torque	1,3Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	2,5mm ²
Connection cross-sect. rigid cable	2,5mm ²
Type of connection	with screw
Type of contacts	2NO

Accessories included

Type of accessory	fault-signal contact
-------------------	----------------------

Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	2
Number of auxiliary contacts as change-over contact	0

Standards

European directive WEEE concerned

Safety

Protection index IP IP20

Use conditions

Operating temperature -25...55 °C