



MZ527N



Alarm contact for motor starter 2C

Technical characteristics

Electric current

Rated current	1 A
Rated current 230 V AC15	3.50 A

Connectivity

Type of connection	Screw terminal
Mounting type	DIN rail adapter

Capacity

Number of modules	0.50
-------------------	------

Connection

Type of contacts	2NO
Cross-section flexible conductor	2.5 mm ²
Cross-section rigid conductor	2.5 mm ²

Voltage

Rated insulation voltage U_i	690 V
Rated impulse withstand voltage U_{imp}	6,000 V
Type voltage supply	AC

Frequency

Frequency	40 - 60 Hz
-----------	------------

Endurance

Number of mechanical operations	10,000
Electric endurance in number of cycles	5,000

Use conditions

Operating temperature	-25 - 55 °C
Storage/transport temperature	-25 - 80 °C

Power

Total power loss under IN	0.20 W
---------------------------	--------

Dimensions

Width	9 mm
Depth	68 mm

Equipment

Number of INV contacts	0
------------------------	---

Number of NC contacts	0
-----------------------	---

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------