



MZ527N



## Alarm contact for motor starter 2C

### Technical characteristics

#### Main electrical features

Rated operational voltage U <sub>e</sub>	220 / 500 V
Type of supply voltage	AC

#### Voltage

Rated insulation voltage	690 V
Rated impulse withstand voltage	6000 V

#### Electric current

Acceptable current rating with AC1	3 A
------------------------------------	-----

#### Dimensions

Depth of installed product	68 mm
Width of installed product	9 mm

#### Power

Total power loss under I <sub>N</sub>	0.2 W
---------------------------------------	-------

#### Endurance

Electric endurance in number of cycles	5000
Number of mechanical operations	10000

#### Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	2
Number of auxiliary contacts as change-over contact	0

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-25...55 °C
-----------------------	-------------