



MZ527N



## Alarm contact for motor starter 2C

### Technical Characteristics

#### Main electrical features

Rated operational voltage Ue	220 / 500 V
Frequency	40/60 Hz
Rated current	1 A
Type of supply voltage	AC

#### Voltage

Rated insulation voltage	690 V
Rated impulse withstand voltage	6000 V

#### Electric current

Acceptable current rating with AC1	3 A
------------------------------------	-----

#### Dimensions

Depth of installed product	68 mm
Width of installed product	9 mm

#### Power

Total power loss under IN	0.2 W
---------------------------	-------

#### Endurance

Electric endurance in number of cycles	5000
Number of mechanical operations	10000

#### Capacity

Number of modules	0.5
-------------------	-----

#### Installation, mounting

Tightening torque	1,3Nm
-------------------	-------

#### Connection

Connection cross-sect. flexible conductor	2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	2,5mm <sup>2</sup>
Type of connection	with screw
Type of contacts	2NO

#### Accessories included

Type of accessory	fault-signal contact
-------------------	----------------------

#### Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	2
Number of auxiliary contacts as change-over contact	0
Can be accessorized	No

#### Standards

European directive WEEE	concerned
-------------------------	-----------

---

**Safety**

Protection index IP

IP20

---

**Use conditions**

Operating temperature

-25...55 °C