



MZ528N

**Under voltage release for motor starter 230V AC**

**Technical characteristics**

**Main electrical features**

Rated operational voltage Ue	230 V
Frequency	50 Hz
Type of supply voltage	AC

**Voltage**

Rated insulation voltage	6000 V
--------------------------	--------

**Dimensions**

Depth of installed product	68 mm
Width of installed product	17.5 mm

**Power**

Total power loss under IN	0.5 W
---------------------------	-------

**Connection**

Connection cross-sect. flexible conductor	2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	2,5mm <sup>2</sup>

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-25...55 °C
-----------------------	-------------