



MZ529N

Under voltage release for motor starter 400V AC

Technical Characteristics

Main electrical features

Rated operational voltage Ue	400 V
Frequency	50 Hz
Type of supply voltage	AC

Voltage

Rated insulation voltage	6000 V
--------------------------	--------

Dimensions

Depth of installed product	68 mm
Width of installed product	17.5 mm

Power

Total power loss under IN	0.5 W
---------------------------	-------

Capacity

Number of modules	1
-------------------	---

Connection

Connection cross-sect. flexible conductor	2,5mm ²
Connection cross-sect. rigid cable	2,5mm ²

Equipment

Can be accessorized	No
---------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-25...55 °C
-----------------------	-------------