



NDN404A



## MCB 4P 10kA/15kA D-4A 4M

### Technical characteristics

#### Architecture

Neutral position	without neutral
Number of poles	4 P
Curve	D

#### Main electrical features

Rated operational voltage U <sub>e</sub>	400 V
Type of supply voltage	AC

#### Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	6000 V

#### Electric current

Rated service breaking capacity I <sub>cs</sub> AC according IEC 60898-1	7.5 kA
Rated service breaking capacity I <sub>cs</sub> under 400V AC according IEC 60947-2	7.5 kA
Rated short circuit breaking capacity I <sub>cn</sub> under 230V AC according IEC60898-1	10 kA

#### Electric current / temperature

Rating current 30°C	4 A
---------------------	-----

#### Dimensions

Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	70 mm

#### Power

Total power loss under I <sub>N</sub>	10.9 W
---------------------------------------	--------

#### Endurance

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

#### Installation, mounting

Tightening torque	2,8Nm
-------------------	-------

#### Equipment

Can be accessorized	Yes
---------------------	-----

#### Standards

**Safety**

Protection index IP

IP20

**Use conditions**

Operating temperature

-25...70 °C