



P22/LSF/2.0

P22 c/w 3 Core 0.75mm² 2 Metre LSOH Lead

Technical characteristics

Main electrical features

| | |
|--|-------------------|
| Rated operational voltage U _e | 207 / 230 / 253 V |
|--|-------------------|

Materials

| | |
|--------|------------|
| Colour | pure white |
|--------|------------|

Connection

| | |
|-----------|---------------------------------|
| Cable End | Prepared - end of barrel closed |
|-----------|---------------------------------|

Cable

| | |
|----------------|----------------------|
| Conductor Size | 0.75 mm ² |
|----------------|----------------------|

Equipment

| | |
|-------------------------------|---|
| Number of terminations -plugs | 3 |
|-------------------------------|---|

| | |
|------------------|-----------------|
| Contact Material | Phosphor Bronze |
|------------------|-----------------|

Use

| | |
|-----------------|--------------|
| Mechanical Load | 5 Kg maximum |
|-----------------|--------------|

Safety

| | |
|----------------|----------|
| Inflammability | UL 94 V0 |
|----------------|----------|