



P64AX

IP20

4 Pin Plug White

Technical Characteristics

Number of poles	4 P
Rated operational voltage Ue	207 / 230 / 253 V
Rated current	6 A
Colour	pure white
Number of terminations -plugs	4
Contact Material	Phosphor Bronze
Mechanical Load	5 Kg maximum
Inflammability	UL 94 V0
Application, usage	Light control