



PCR2000/2.0

PCR2000 c/w 3 Core 0.75mm² 2m PVC Lead

Technical characteristics

Architecture

Number of poles	3
-----------------	---

Voltage

Max. operating voltage	240 V
------------------------	-------

Electric current

Rated current	6 A
---------------	-----

Cable

Cable diameter	7 mm
----------------	------

Cable permanent temperature resistant to	90 °C
--	-------

Dimensions

Length	2,000 mm
--------	----------

Connection

Conductor cross-section	0.75 - 0.75 mm ²
-------------------------	-----------------------------

Equipment

Mechanical coding	Yes
-------------------	-----

Type cable side 1	Plug
-------------------	------

Type cable side 2	Free conductor end
-------------------	--------------------

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
---	---

Materials

Colour	White
--------	-------