



SBN490

4-pole, 100A Modular Switch

Technical characteristics

Architecture

Neutral position	without neutral
Number of poles	4 P

Main electrical features

Rated operational voltage U _e	400 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	440 V
Rated impulse withstand voltage	6000 V

Dimensions

Depth of installed product	69 mm
Height of installed product	83 mm
Width of installed product	70 mm

Power

Total power loss under I _N	22 W
---------------------------------------	------

Endurance

Electrical durability at nominal load in AC22 in operating cycles	2500
Number of mechanical operations	40000

Installation, mounting

Tightening torque	3,6Nm
-------------------	-------

Connection

Type of connection	with screw
--------------------	------------

Standards

Standard text	IEC 60947-3
---------------	-------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-20...50 °C
-----------------------	-------------