




SF263



## 2 pole Changeoverswitch 63A I-O-II

### Technical characteristics

#### Architecture

Number of poles	2 P
-----------------	-----

#### Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

#### Dimensions

Depth of installed product	72 mm
Height of installed product	90 mm
Width of installed product	71.5 mm

#### Power

Total power loss under IN	3.6 W
---------------------------	-------

#### Endurance

Number of mechanical operations	100000
---------------------------------	--------

#### Installation, mounting

Tightening torque	2,9Nm
-------------------	-------

#### Connection

Connection cross-sect. flexible conductor	16mm <sup>2</sup>
Connection cross-sect. rigid cable	25mm <sup>2</sup>
Type of contacts	changeover with zero position

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-20...50 °C
-----------------------	-------------