



SFT225

2-pole, 25A Centre Off Modular Changeover Switch with Top Common Point

Technical Characteristics

Number of poles	2 P
Type of pole	2 P
Rated operational voltage Ue	230 V
Frequency	50/60 Hz
Rated current	25 A
Rated insulation voltage	440 V
Rated impulse withstand voltage	4000 V
Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	35 mm
Total power loss under I _N	1.8 W
Electrical durability at nominal load in AC22 in operating cycles	25000
Number of mechanical operations	200000
Number of modules	2
Tightening torque	1,8Nm
Connection cross-sect. flexible conductor	1,5 / 10mm ²
Connection cross-sect. rigid cable	1,5 / 16mm ²
Type of connection	with screw
Can be accessorized	No
Standard text	IEC 60947-3 IEC/EN 60669-1
European directive WEEE	concerned
Protection index IP	IP20
Operating temperature	-20...50 °C